


MEDL40227-MKX8(全灯)  
 器具全光束:6120lm  
 ランプ:LDL40S・N/22/34/PC


### 配光曲線図

光度 cd/1000lm

— A-A  
 — B-B  
 — C-C



光度(cd/1000lm)			
	A-A	B-B	C-C
-90°	15	14	14
-80°	76	42	70
-70°	130	87	126
-60°	177	130	154
-50°	198	166	182
-40°	217	198	206
-30°	232	222	227
-20°	245	242	242
-10°	254	254	254
0°	258	258	258
10°	254	254	254
20°	245	242	242
30°	232	222	227
40°	217	198	206
50°	198	166	182
60°	177	130	154
70°	130	87	126
80°	76	42	70
90°	15	14	14



器具効率	最大取付間隔	保守率		
UP 0.4 %	A-A 1.34 H	良	中	否
DN 91.4 %	B-B 1.29 H	74	70	64

反射率 (%)	天井	80						70						50						30				0
	壁	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	30	10	30	10	0
	床	30		10				30			10			30			10			30		10		0
室指数	照明率 U ( × 0.01 )																							
0.6	40	31	26	38	31	25	39	31	26	38	30	25	38	31	25	36	30	25	30	25	30	25	23	
0.8	51	41	35	48	40	34	50	41	35	47	39	34	48	40	34	45	39	34	39	34	39	34	31	
1.0	59	50	43	55	47	42	58	49	43	54	47	41	55	48	42	52	46	41	46	41	46	41	39	
1.25	68	58	52	62	55	49	66	57	51	61	54	49	63	56	50	59	53	48	54	49	53	48	46	
1.5	74	65	58	67	60	55	72	64	57	66	60	55	68	62	56	64	59	54	59	55	59	54	51	
2.0	83	75	69	74	69	64	81	74	68	73	68	63	77	71	66	71	67	63	68	64	67	63	60	
2.5	90	83	77	79	74	70	87	81	75	78	74	70	82	77	73	76	72	69	74	70	72	69	65	
3.0	95	89	83	83	79	75	92	86	81	82	78	75	87	82	78	80	77	74	79	75	77	74	70	
4.0	101	96	92	88	85	82	98	94	90	87	84	81	92	89	86	85	82	80	84	82	82	80	76	
5.0	105	101	97	91	88	86	102	98	95	89	87	85	96	93	90	87	85	83	88	86	85	83	80	