


MEDL40224-MKX8(全灯)  
 器具全光束:6450lm  
 ランプ:LDL40S・N/22/34/PC


### 配光曲線図

光度 cd/1000lm

— A-A  
 — B-B  
 — C-C



光度(cd/1000lm)			
	A-A	B-B	C-C
-90°	14	14	16
-80°	66	42	62
-70°	108	88	124
-60°	176	130	157
-50°	200	166	184
-40°	219	197	208
-30°	236	223	229
-20°	246	242	244
-10°	254	254	254
0°	257	257	257
10°	254	254	254
20°	246	242	244
30°	236	223	229
40°	219	197	208
50°	200	166	184
60°	176	130	157
70°	108	88	124
80°	66	42	62
90°	14	14	16



器具効率	最大取付間隔	保守率		
UP 0.4 %	A-A 1.36 H	良	中	否
DN 90.4 %	B-B 1.29 H	81	81	71

反射率 (%)	天井	80						70						50						30				0
	壁	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	30	10	30	10	0
	床	30		10				30			10			30			10			30		10		0
室指数	照明率 U ( × 0.01 )																							
0.6	40	31	26	38	31	25	39	31	26	37	30	25	38	31	25	36	30	25	30	25	30	25	23	
0.8	50	41	35	47	40	34	49	41	35	47	39	34	48	40	34	45	39	34	39	34	39	34	32	
1.0	59	50	43	55	47	42	58	49	43	54	47	41	55	48	42	52	46	41	46	41	46	41	39	
1.25	67	58	51	62	55	49	66	57	51	61	54	49	63	55	50	59	53	48	54	49	53	48	46	
1.5	73	65	58	67	60	55	72	64	57	66	59	54	68	61	56	64	58	54	59	55	58	54	51	
2.0	83	75	68	74	68	63	80	73	67	73	67	63	76	70	65	71	66	62	67	63	66	62	59	
2.5	89	82	76	78	74	69	86	80	74	77	73	69	82	76	72	75	71	68	73	69	71	68	65	
3.0	94	87	82	82	78	74	91	85	80	81	77	74	86	81	77	79	76	73	77	74	76	73	69	
4.0	100	95	90	86	83	80	97	92	88	85	82	80	91	87	84	83	81	78	83	80	81	78	75	
5.0	104	99	95	89	86	84	100	96	93	88	86	83	94	91	88	86	84	82	86	84	84	82	78	